

LEWA ecodos® sanitary

Diaphragm pump series







- hermetically tight
- accurate, repeatable metering
- low hold-up volume
- low shear handling of fluids
- reliable and economical
- low maintenance







LEWA pump design setting the standards for industry



One pump for many applications: Production of jellied sweets.



Metering of colours, flavours, or preservatives.



Transfer of mustard and other viscous products.

Performance

LEWA ecodos® sanitary pumps provide fluid metering and transfer from 0,4 l/h to 1.500 l/h per pump head. Up to six pumps can be multiplexed for additional capacity or to reduce pulsation. Whether using open loop control for simple systems or closed loop control for more complex applications, the end result is a process with exactly metered ingredients to achieve consistent product quality. LEWA ecodos® sanitary pumps are suited to applications with discharge pressures up to 20 bar.

Main features of the pump

- Sealless, and hermetically tight
- No sliding seals or packing
- Low hold-up volume
- Suitable for CIP
- Run-dry safe
- Easy disassembly and re-assembly of the pumping chamber
- Multiplex capable
- Compact for small footprint
- Long uptimes

Surface finishes

All pump head components are manufactured of 1.4571 (316 Ti) stainless steel, and wetted surfaces are mechanically polished to sanitary industry standards (≤ 0,8 µm). This provides corrosion resistant and easy-to-clean surfaces.

Leaktight and fail-safe

The LEWA ecodos® "safety diaphragm" is made of pure, solid pure PTFE compatible with biological tissue (USP Class VI). Should perforation of the working diaphragm layer occur, an immediate signal is given by the diaphragm condition monitor for shutdown.

FDA approved materials

All materials of construction wetted by

the process fluids are FDA approved and therefore compatible with food and drug products.

Tri-clamp or other sanitary fittings

For easy integration into existing or new process lines, tri-clamp or other design sanitary fittings are available to meet user requirements.

Proper documentation

Extensive documentation is a matter of course at LEWA. Included with the operating manuals are technical data sheets, cross-sectional drawings, material traceability and wear and spare parts lists. Test reports, pressure tests and output diagrams are available as options.



LEWA pumps have many configurations that run the range from simple metering to skids for introducing micro-ingredients.



Proportional blending of liquid ingredients.



Complex systems for proportional blending or transfer of multiple product streams

Proportional blending

LEWA metering technology satisfies customer requirements for continuous production, resulting in cost savings and waste reduction. Whether for simultaneous blending of different ingredient streams in proportional amounts, or for injecting accurate and repeatable amounts of micro-ingredients into a main process stream, LEWA ecodos® pumps have been proven in operation for many years.

Fluid transfer

LEWA diaphragm pumping technology makes it possible to handle shear-sensitive and expensive ingredients in a hermetically sealed pumping environment and with gentle pumping action. Due to the extreme low hold-up volume in the pump head and the pressure-stiff characteristics of diaphragm pumps, fluids pass through the pump head quickly and without inefficient slippage.





For short distances: LEWA at your service worldwide

Germany / Headquarter LEWA GmbH

Ulmer Str. 10 71229 Leonberg Phone +49 7152 14-0 +49 7152 14-1303 lewa@lewa.de www.lewa.de

Japan / Headquarter ■ NIKKISO CO. LTD.

3-43-2, Ebisu, Shibuya-ku, Tokyo 150-8677 Phone +81 3 3443-3711 Fax +81 3 3473-4963 www nikkiso com



■ LEWA Pumpen GmbH

1150 Vienna Phone +43 1 8773 040-0 info@lewa at www.lewa.at

LEWA Bombas Ltda.

09951-970 Diadema/SP Phone +55 11 4075 9999 info@lewa.com.br www.lewa.com.br

Bulgaria

■ LEWA - Technical Office Sofia

1421 Sofia Phone +359 2 8654088 lewa.bg@lewa.at www.lewa.bg

LEWA Pumps (Dalian) Co., Ltd.

11 6600 Dalian Phone +86 411 8758-1477 sales@lewa.cn www.lewa.cn

Czech Republic

LEWA Pumpen spol. s.r.o.

602 00 Brno Phone +420 5 432360-52 office@lewa.cz www.lewa.cz

France

LEWA S.A.S.

78500 Sartrouville Phone +33 1 308674-80 info@lewa.fr www.lewa.fr

LEWA HOV GmbH + Co KG

71229 Leonberg Phone +49 7152 6091-0 hov@hov.de www.hov.de

Hungary

■ LEWA – Hungarian Representative

2040 Budaörs Phone +36 23 880 975 info@lewa.hu www.lewa.hu

LEWA S.R.L.

20017 Mazzo di Rho (Mi) Phone +39 02 93468-61 info@lewa.it www.lewa.it

Mexico

■ LEWA México – Technical Office

01210 México D.F. Phone +52 55 917292-10 info@lewa.es www.lewa.es

Norway

LEWA AS

4319 Sandnes Phone +47 529091-00 info@lewa.no www.lewa.no

Poland

LEWA Sp. z o.o.

00-159 Warsaw Phone +48 22 6358-204 info@lewa.pl www.lewa.pl

LEWA Romania s.r.l.

050579 Bucharest Phone +40 21 4107-340 info@lewa ro www.lewa.ro

Singapore

LEWA PTE LTD

Singapore 129808 Phone +65 686-17127 info@lewa.sg www.lewa.sg

Singapore

Pump Alliance PTE LTD (J. V.)

Singapore 129808 Phone +65 6468 6802 pbeddard@pumpalliance.com www.lewa.sg

Spain

LEWA Hispania, S.L.

08020 Barcelona Phone +34 93 22477-40 info@lewa.es www.lewa.es

Switzerland

LEWA Pumpen AG

4153 Reinach 1 Phone +41 61 7179 4-00 info@lewa-pumpen.ch www.lewa-pumpen.ch

U.A.E. / Dubai

LEWA GmbH (LEWA Branch)

Dubai Airport Free Zone Phone +971 4 2993969 lewa@lewa-dubai.ae www.lewa.ae

■ LEWA Ukraine LC

03039 Kiev Phone +380 44 52796-31 office@lewa.kiev.ua http://www.lewa.com/ukraine/ua/2482/

USA / North- and Middle America

LEWA, Inc.

Holliston, MA 01746 Phone +1 508 429-7403 sales@lewa-inc.com www.lewa-inc.com

USA/Gulf Coast Sales & Service Center ■ LEWA, Inc

Houston, TX 77086 Phone +1 713 577-5392 sales@lewa-inc.com www.lewa-inc.com

■ CPE Holdings, Inc.

Houston, TX 77086 Phone +1 713 673-5161 rfletcher@capitalprocess.com www.capitalprocess.com

Find more LEWA subsidiaries at www.lewa.com